



Remote Mounting Distances

→ Emergency Lighting News for the **bodine®** Manufacturing Representatives

The chart below provides remote mounting information at a glance. Please contact Bodine Technical Support at 888-263-4638 if you have any questions or need further assistance.

Product	≤ 80' or up to half the AC ballast remote mounting distance, whichever is less	≤ 50' or up to half the AC ballast remote mounting distance, whichever is less	≤ 30' or up to half the AC ballast remote mounting distance, whichever is less	≤ 10' or up to half the AC ballast remote mounting distance, whichever is less	≤ 6' or up to half the AC ballast remote mounting distance, whichever is less
ARC Keeper® Probe-Start 400 W*	•				
ARC Keeper® Probe-Start 250 W		•			
ARC Keeper® Probe-Start 175 W			•		
B30 / B30ST		•			
B33		•			
B35ST		•			
B50 / B50ST		•			
B60		•			
B74CST		•			
B100		•			
GEN1		•			
GEN3		•			
B413		•			
B426		•			
B463		•			
CF94		•			
CB80 & 90			•		
B94 / BDL94C		•			
B94G / B94CG				•	
B4CFG				•	
B84CG				•	
B4CF1				•	
B4CF2				•	
LP600				•	
LP600STU				•	
LP550				•	
LP500				•	
LP400		•			
B55				•	
BHD55U				•	
CF94G				•	
B75 / B75C					•

*Contact Bodine Tech Support for ARC Keeper Pulse-Start remote mounting distances.
Damp versions of emergency ballasts have the same remote mounting distances as their dry counterparts.